


### Product Description: 1.5kW Oil free column heater with choice of heats & thermostat

Unique oil free technology

Fast Warm Up

Energy Saving


Lightweight



Unique Fin Design



Easy to Use Controls



<b>Product Category:</b>	Portable Heating
<b>Product Type:</b>	Oil Free Column Heater
<b>Brand:</b>	Dimplex
<b>Model Reference:</b>	OFRC15c
<b>Model/Range Name:</b>	N/A
<b>Barcode:</b>	5011139023803
<b>Commodity Code:</b>	85162950
<b>Country of Origin:</b>	PRC
<b>Approvals:</b>	CE, BEAB
<b>Guarantee Period:</b>	3 years

### PRODUCT FEATURES

<b>Output (kW/Watts):</b>	1.5kW / 1500W
<b>Variable Thermostat:</b>	Y
<b>Heat Settings:</b>	2 - 1kW / 1.5kW
<b>Cool Blow Setting:</b>	N
<b>Timer:</b>	N
<b>Turbo Fan Boost:</b>	N
<b>ECC Electronic Climate Control:</b>	N
<b>LCD / LED Display:</b>	N
<b>Oscillation Function:</b>	N
<b>Neon Indicator:</b>	Y - Mains
<b>Frost Setting:</b>	Y
<b>Freestanding:</b>	Y

<b>Wall Mountable:</b>	N
<b>Cable Tidy:</b>	Y
<b>Easy Glide Castors:</b>	Y
<b>Carry Handles:</b>	Y
<b>Remote Control:</b>	N
<b>Batteries Included:</b>	N
<b>Safety Cut Out:</b>	Y
<b>Finish/Colour:</b>	Cream
<b>Power Cord Length:</b>	1.5m
<b>Element Type:</b>	Sheathed
<b>Core Materials:</b>	Steel
<b>Other Features:</b>	On/Off Switch

### UNPACKED DIMENSIONS & WEIGHT

<b>Height (mm):</b>	622 - A	<b>Depth (mm):</b>	280 - C
<b>Width (mm):</b>	350 - B	<b>Weight (kg):</b>	8.52

### PACKED DIMENSIONS & WEIGHT

<b>Height (mm):</b>	650	<b>Depth (mm):</b>	150
<b>Width (mm):</b>	465	<b>Weight (kg):</b>	9.50

### TI HI

<b>TI:</b>	14
<b>HI (at 1.0m)</b>	14
<b>HI (at 1.2m):</b>	14
<b>HI (at 1.6m):</b>	28
<b>HI (at 1.8m):</b>	28
<b>HI (at 2.4m):</b>	42

### PACK & ACCESSORY COMPOSITION WEIGHTS

<b>Cardboard:</b>	847g
<b>EPS / Plastic:</b>	81g / 43g
<b>Batteries:</b>	N/A
<b>Remote Control:</b>	N/A
<b>Strapping / Staples:</b>	N/A
<b>Instruction Booklet:</b>	10g