



50W Dimmable DALI LED Driver

SOLOdrive 560/S is a DALI compatible, constant current LED driver with two LED outputs that are controlled as a single ballast. Dimming is beautiful - smooth all the way down to 0. SOLOdrive is programmable to suit a wide application area. Its two LED outputs offer the possibility of driving a very high power 50W LED array connected to a single output, or driving two strings of 15 LEDs at 350mA. LEDcode allows easy extension of the SOLOdrive's feature set with time, motion and brightness based intelligence.

Applications

- Office lighting
- Next-generation 'T5' luminaires
- Architectural lighting
- Hospitality lighting
- Low Bay lighting
- Signage / advertising lighting
- Retail lighting
- Public area / park / street lighting
- Display lighting

Features & benefits

Input

- Voltage: 120 - 277 VAC
- Current, max: 0.7A
- Frequency: 50/60Hz



SOLOdrive 560/M

Output

- Class 2 LED outputs (x2)
- Voltage: 55V typ
- Current range: settable from 200mA to 1,050mA for each LED output separately
- Power: 50W max



SOLOdrive 560/S

General

- Power factor: > 0.9
- DALI compatible (IEC 62386-101/102/207)
- Hybrid HydraDrive: efficient, smooth and flicker-free dimming
- Full dimming control: 100% to 0%, choice of linear or logarithmic dimming curve
- Highly efficient over a wide power and voltage range: 89% at full load, ≥ 85% above 50% load
- Maximum (rated) power available over wide LED voltage (30-55V) and LED current range (200-1,050mA)
- NTC interface for robust thermal management
- LEDcode: programming interface (LED output current, NTC temperature, dimming curve, minimum dimming level) and sensor/extended feature set interface



SOLOdrive 560/A

Product offering

Description

- SOLOdrive AC, 50W, DALI, 1 ballast, constant current, 2x 60V LED outputs, long metal
- SOLOdrive AC, 50W, DALI, 1 ballast, constant current, 2x 60V LED outputs, square metal
- SOLOdrive AC, 50W, DALI, 1 ballast, constant current, 2x 60V LED outputs, square metal/plastic

Product

- SOLO 560/M
- SOLO 560/S
- SOLO 560/A


Order no.

- SL0560M1
- SL0560S1
- SL0560A1

Dimensions, weight, packaging


SOLOdrive 560/M

- Weight: 360 g, 12.7 oz
- Packaging: 4, 10 or 40 pcs/carton




SOLOdrive 560/S

- Weight: 350 g, 12.35 oz
- Packaging: 4, 10 or 40 pcs/carton



SOLOdrive 560/A

- Weight: 372 g, 13.12 oz
- Packaging: 4, 10 or 40 pcs/carton



Connections

Connectors

- LED outputs: + and - (x2)
- LEDcode / NTC: + and -
- DALI: + and - (x2)
- Power: Line, Neutral and Ground

Wiring

- Cross section: 0.5 - 1.5 mm², AWG 20 - 16
- Strip length: 9 mm / 0.35 in.

LEDcode configuration

- USB-LEDcode interface: TOOLbox pro (part number: TLU20502)
- FluxTool software: for Mac and PC freely downloadable from www.eldoled.com/fluxtool

Other information

Certifications

- CE
- IEC 61347, IEC 62384, EN 55015, EN 55022, IEC 61000-3-2, IEC 61547, IEC 62386-207
- UL: Recognized Component for US and Canada (file no. E333135), according to UL1310 and UL8750. US: Class 2 output. Canada: Non-Class 2 output. (SOLOdrive 560/M pending.)
- ENEC: pending

Environmental ratings

- Ta range: -20°C...+50°C / -4°F...+122°F
- Tc max: 85°C / 185°F
- For use in damp and dry locations

Control compatibility

- DALI control gear



Europe, Rest of World

eldoLED Europe bv
Luchthavenweg 18a
NL-5657 EB Eindhoven
The Netherlands
T: +31 40 2054050
F: +31 40 2054058

North America

eldoLED America, Inc.
1762 Technology Drive #226
San Jose, CA 95110
USA
T: +1 408 451 9333
F: +1 408 451 9335

Other documentation and support

Visit www.eldoled.com/ACsupport for further documentation such as quick start guide, wiring diagram, tech sheet and 3D IGES files.

Warranty

eldoLED represents and warrants that for a period of 3 (three) years, as of the date of invoice, Products materially meet the specifications and specifically agreed upon quality, both as stated in the applicable datasheet and/or written design-in specifications, or as stated in writing otherwise by eldoLED, provided that these specifications are explicitly designated by eldoLED as "warranted specifications".

For the complete warranty text, visit www.eldoled.com/terms.