



# GelCap

## Motor Connection Kit (1000V)

### Energy Division

Tyco Electronics' GelCap motor connection kits provide quick installation, dependable performance, and easy reentry.

GelCap motor connection kits quickly and conveniently insulate, seal, and protect stub splice connections up to 1000 volts. The robust yet compact design was engineered to handle the harsh environment of motor connections. GelCap kits are equally well suited to many other connection applications including street light connections.

#### **Fast and easy installation**

GelCap motor connection kits provide for fast installation. Simply push the cover down over the connection and snap the clamp closed. The PowerGel sealing gel is already in the cap, no extra material or grease is required.

#### **Easy reentry**

The corner of the stub connection is easy to reenter as the PowerGel sealing gel pulls away leaving a clean connection. Reentry is also safer than other methods because no sharp objects or cutting tools are required for removal of the cap.

#### **PowerGel sealing gel technology**

The GelCap motor connection kits feature revolutionary PowerGel sealing gel which provides an excellent moisture seal over a wide temperature range (-40°C to 105°C). PowerGel sealing gel has excellent insulating properties and the added benefit of acting as a vibration damper.

#### **Common uses**

- Motor connections
- Street lighting
- Over wire nuts for sealing
- Irrigation systems
- HVAC
- Outdoor lighting

## Product Selection

Kit Description	Feeder Conductor Size (mm <sup>2</sup> )
GelCap 1*	#16 – #10 AWG (1.5 – 5)
GelCap 2	#8 – #2 AWG (8 – 35)
GelCap 3	#2 – #4/0 AWG (35 – 105)
GelCap 4	250 – 500 kcmil (125 – 250)


\* For wire sizes #16 – #10 the unique design of the "GelCap 1" kit saves space by allowing all three phase connections to be installed in one cover. Product sizes 2, 3, and 4 include one cap per phase.

## Product Performance

GelCap motor connection kits meet the following requirements:

Testing	Test Conditions
Chemical Resistance	ASTM D543, Sulfuric acid, Sodium hydroxide, Transformer and motor oil
Ozone Resistance	ASTM D1149, 120 hours @40°C, 50pphm
Accelerated Aging	ASTM D2671
UV Resistance	ASTM G53, UVB, 4000 hours, 4 hour on/off cycle
Abrasion Resistance	2040 gm wt., 4000 cycles, 5% max thickness loss

Related Product Information: EDR-5334 Test Report



Tyco Electronics Corporation  
 8000 Purfoy Road  
 Fuquay Varina, NC 27526-9349  
 Tel: 800.327.6996  
 Fax: 800.527.8350  
 E-mail: naenergy@tycoelectronics.com  
<http://energy.tycoelectronics.com/powergel>  
[www.tycoelectronics.com](http://www.tycoelectronics.com)

All of the above information, including drawings, illustrations and graphic designs, reflects our present understanding and is to the best of our knowledge and belief correct and reliable. Users, however, should independently evaluate the suitability of each product for the desired application. Under no circumstances does this constitute an assurance of any particular quality or performance. Such an assurance is only provided in the context of our product specifications or explicit contractual arrangements. Our liability for these products is set forth in our standard terms and conditions of sale. GelCap, TE logo and Tyco Electronics are trademarks.

Energy Division – a pioneer in the development of economical solutions for the electrical power industry. Our product range includes: Cable accessories, connectors & fittings, electrical equipment, instruments, lighting controls, insulators & insulation enhancement and surge arresters.