




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A3	REVISED PER ECO-12-014757	14AUG2012	KH	MB		



RECOMMENDED PANEL CUTOUT
 3.2mm MAXIMUM PANEL THICKNESS



SHIELDED	2008615-2
UNSHIELDED	2008615-1
DESCRIPTION	PART NUMBER

- CONNECTOR MAY BE FRONT OR REAR PANEL MOUNTED. VIEWS SHOW PANEL NUT AND GASKET LOCATION FOR THE REAR PANEL MOUNTED VERSION.
- COUPLER LINES CROSSOVER BETWEEN POSTS.
- PANEL NUT AND PANEL GASKET ARE PACKAGED ASSEMBLED IN POLYBAG.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 01APR2008	TE Connectivity													
DIMENSIONS: mm		CHK C. HERTZLER 01APR2008														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. HERTZLER 01APR2008														
<table border="1"> <tr><td>0 PLC</td><td>±1.0</td></tr> <tr><td>1 PLC</td><td>±0.2</td></tr> <tr><td>2 PLC</td><td>±0.10</td></tr> <tr><td>3 PLC</td><td>±0.000</td></tr> <tr><td>4 PLC</td><td>±0.0000</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td></td></tr> </table>		0 PLC		±1.0	1 PLC	±0.2	2 PLC	±0.10	3 PLC	±0.000	4 PLC	±0.0000	ANGLES	±	FINISH	
0 PLC	±1.0															
1 PLC	±0.2															
2 PLC	±0.10															
3 PLC	±0.000															
4 PLC	±0.0000															
ANGLES	±															
FINISH																
MATERIAL		PRODUCT SPEC	SIZE A2													
		APPLICATION SPEC	CAGE CODE 00779													
		WEIGHT	DRAWING NO C-2008615													
		CUSTOMER DRAWING	RESTRICTED TO													
			SCALE 3:1 SHEET 1 OF 1 REV A3													