

INFORMATIONS PRODUITS

Application

Wiring all types of sound systems.
For fixed and mobile installations.
100 Volts installations.
Conductor identification by colour (Red/Black) (Shape 1) or mechanical differentiation (Shape 2).

Electrical properties

Operating tension : < 900 V

Tension test : 2500 V

Electrical resistance at 20°C :

0,5 mm ² :	61,9 Ω/km
0,75 mm ² :	36,1 Ω/km
1,0 mm ² :	27,1 Ω/km
1,5 mm ² :	18,1 Ω/km

Mechanical characteristics



Temperature range :
Static use : - 25°C → + 70°C
Dynamic use : - 5°C → + 70°C






Minimum bending radius :
8 x Ø



Conform to RoHS directive

Références produits

		Stranded Conductor		Shape	Colours
4030.5082 N / B	2 x 0,50	14 x 0,20 mm	1,8 x 3,7	2	N : black / B: white
4030.4008	2 x 0,50	14 x 0,20 mm	1,8 x 3,7	1	Red / Black
4030.5067 N/G/B	2 x 0,75	24 x 0,20 mm	2,1 x 4,2	2	N : black / G :grey / B: white
4030.4089	2 x 0,75	24 x 0,20mm	2,1 x 4,2	1	Red / Black
4030.5122 N/G/B	2 x 1,0	32 x 0,20 mm	2,4 x 4,8	2	N : black / G :grey / B: white
4030.4150	2 x 1,0	32 x 0,20 mm	2,4 x 4,8	1	Red / Black
4030.5126 N/G/B	2 x 1,5	48 x 0,20 mm	2,6 x 5,2	2	N : black / G :grey / B: white
4030.7126 RN	2 x 1,5	48 x 0,20 mm	2,6 x 5,2	1	Red / Black