

CLAMPING VICES SPANNFIX MAXI

Heavy-duty vice SPANNFIX MAXI on ball-and-socket joint rotatable in any direction and capable of being set securely.

The same operations, the same flexibility and the universal use as the Spannfix small vice also distinguish the large models. Suitable for working on larger and heavier workpieces, e. g. in the metal working and wood processing industry.



9-225

9-225 **BERNSTEIN SPANNFIX VICE MAXI** screw-on

for work benches with a max. table thickness of 85 mm.

Technical data: Clamping pressure 300 kp
Clamping capacity 100 mm
Clamping depth 50 mm
Jaw width 100 mm
interchangeable steel jaws
smooth and fluted
Alu- and plastic jaws on request

Weight: 4.000 kg



9-226

9-226 **BERNSTEIN SPANNFIX VICE MAXI** for permanent mounting using bolts

Technical data: as 9-225
Size of base: 190 x 155 mm

Weight: 3.600 kg



9-227

SPANNFIX MAXI FOR SPECIAL POSITIONINGS

The Spannfix MAXI ball-and-socket joint base enables an exact and secure adjustment e. g. for heavy instruments in all directions.

9-227 **SPANNFIX MAXI universal clamp** mounting ball joint base with threaded stud M 12 x 1.5 for screwing onto work benches with a max. table thickness of 85 mm

Weight: 2.220 kg

9-228 **SPANNFIX MAXI bench mounted base** with universal ball joint and threaded stud M 12 x 1.5 for permanent mounting using bolts

Size of base: 190 x 155 mm

Weight: 1.850 kg



9-228