





**Productname :** PLASTIK 70 **Creationdate :** 30.11.18 Version : 1.1  
**Ref.Nr.:** BDS002139\_3\_20181130 (EN) **Replaces:** BDS002139\_20170629

Pressurised container: May burst if heated.  
Classification is based on test data.  
**Health:** Eye irritation, category 2  
Causes serious eye irritation.  
Specific target organ toxicity - single exposure, category 3  
May cause drowsiness or dizziness.  
Classification based on calculation method.  
**Environment:** Not classified  
Classification based on calculation method.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

**Product identifier:** Contains:  
n-butyl acetate  
ethyl acetate

**Hazard pictogram(s):**  

**Signal word:** Danger

**Hazard statement(s):** H222 : Extremely flammable aerosol.  
H229 : Pressurised container: May burst if heated.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.

**Precautionary statement(s):** P102 : Keep out of reach of children.  
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P211 : Do not spray on an open flame or other ignition source.  
P251 : Do not pierce or burn, even after use.  
P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.  
P271 : Use only outdoors or in a well-ventilated area.  
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.  
P501-2 : Dispose of contents/container to an authorised waste collection point.

**Supplemental Hazard information:** Repeated exposure may cause skin dryness or cracking.

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

**Productname :** PLASTIK 70  
**Ref.Nr.:** BDS002139\_3\_20181130 (EN)

**Creationdate :** 30.11.18 Version : 1.1  
**Replaces:** BDS002139\_20170629

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	25-50	Flam. Liq. 3, STOT SE 3	H226,H336	
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	25-50	Press. Gas, Flam. Gas 1	H280,H220	K,G
1-methoxy-2-propanol; monopropylene glycol methyl ether	01-2119457435-35	107-98-2	203-539-1	10-25	Flam. Liq. 3, STOT SE 3	H226,H336	A
ethyl acetate	01-2119475103-46	141-78-6	205-500-4	10-25	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B

**Explanation notes**

A : substance with Community workplace exposure limit  
B : substance with national established workplace exposure limit  
G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006  
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed



**Productname :** PLASTIK 70  
**Ref.Nr.:** BDS002139\_3\_20181130 (EN)

**Creationdate :** 30.11.18 Version : 1.1  
**Replaces:** BDS002139\_20170629

**General Advice :** If you feel unwell, seek medical advice (show the label where possible)  
If symptoms persist always call a doctor

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage



**Productname :** PLASTIK 70  
**Ref.Nr.:** BDS002139\_3\_20181130 (EN)  
**Creationdate :** 30.11.18 Version : 1.1  
**Replaces:** BDS002139\_20170629

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
 Take precautionary measures against static discharges  
 Equipment should be earthed  
 Use explosion-proof electrical/ventilating/lighting/.../equipment.  
 Use only non-sparking tools.  
 Do not breathe aerosols or vapours.  
 Ensure adequate ventilation  
 Avoid contact with skin and eyes.  
 Wash thoroughly after use  
 Wear protective gloves/protective clothing/eye protection/face protection.  
 Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
 Keep out of reach of children.

### 7.3. Specific end use(s)

Anti Corrosion Products

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm

### 8.2. Exposure controls

**Control procedures :** Ensure adequate ventilation  
 Keep away from heat and sources of ignition  
 Take precautionary measures against static discharges

**Personal protection :** Take precautions to avoid contact with skin and eyes when handling the product.  
 Ensure adequate ventilation  
 Wear suitable protective gloves

**inhalation :** In case of insufficient ventilation, wear suitable respiratory equipment.



**Productname :** PLASTIK 70  
**Ref.Nr.:** BDS002139\_3\_20181130 (EN)  
**Creationdate :** 30.11.18 Version : 1.1  
**Replaces:** BDS002139\_20170629

recommended respiratory protection: Air purifying respirator equipped with organic gas/vapor cartridge (type A)

**hands and skin :** When handling the product wear chemical-resistant gloves (standard EN 374).  
The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.

Recommended gloves: (polyvinylalcohol)

**eyes :** Wear safety eyewear according to EN 166.

**Environmental protection:** Avoid release to the environment.  
Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

**Apperance : physical state :** Propane/butane propelled liquid.

**colour :** Colorless.

**odour :** Solvent.

**pH :** Not applicable.

**Boiling point/range :** Not available.

**Flash point :** - 4 °C (Closed Cup)

**Evaporation rate :** Not available.

**Explosion limits : upper limit :** Not available.

**lower limit :** Not available.

**Vapour pressure :** Not available.

**Relative density :** 0.919 g/cm<sup>3</sup> (@ 20°C).

**Solubility in water :** Insoluble in water

**Auto-ignition :** > 200 °C

**Viscosity :** Not available.

### 9.2. Other information

**VOC = volatile organic compounds** 700 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable



Productname : PLASTIK 70      Creationdate : 30.11.18 Version : 1.1  
 Ref.Nr.: BDS002139\_3\_20181130 (EN)      Replaces: BDS002139\_20170629

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

<b>acute toxicity:</b>	based on available data the classification criteria are not met
<b>skin corrosion/irritation:</b>	based on available data the classification criteria are not met
<b>serious eye damage/irritation:</b>	Causes serious eye irritation.
<b>respiratory or skin sensitisation:</b>	based on available data the classification criteria are not met
<b>germ cell mutagenicity:</b>	based on available data the classification criteria are not met
<b>carcinogenicity:</b>	based on available data the classification criteria are not met
<b>toxicity for reproduction:</b>	based on available data the classification criteria are not met
<b>STOT-single exposure:</b>	May cause drowsiness or dizziness.
<b>STOT repeated exposure:</b>	based on available data the classification criteria are not met
<b>aspiration hazard:</b>	based on available data the classification criteria are not met

### Information on likely routes of exposure:

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances
<b>Skin contact :</b>	May cause irritation.
<b>Eye contact :</b>	Irritating to eyes

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg
		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg



**Productname :** PLASTIK 70  
**Ref.Nr.:** BDS002139\_3\_20181130 (EN)

**Creationdate :** 30.11.18 Version : 1.1  
**Replaces:** BDS002139\_20170629

n-butyl acetate	123-86-4	LD50 oral rat	10760 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 1400 mg/kg
ethyl acetate	141-78-6	LD50 oral rat	5620 mg/kg
		LC50 inhal.rat	30 mg/l
		LD50 derm.rabit	> 20000 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l
ethyl acetate	141-78-6	IC50 algae	5600 mg/l
		LC50 fish	230 mg/l
		EC50 daphnia	610 mg/l

### 12.2. Persistence and degradability

No experimental data available

### 12.3. Bioaccumulative potential

No experimental data available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No experimental data available





Productname : PLASTIK 70  
Ref.Nr.: BDS002139\_3\_20181130 (EN)

Creationdate : 30.11.18 Version : 1.1  
Replaces: BDS002139\_20170629

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**National regulations :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.



Productname : PLASTIK 70  
Ref.Nr.: BDS002139\_3\_20181130 (EN)

Creationdate : 30.11.18 Version : 1.1  
Replaces: BDS002139\_20170629

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

### 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H225 : Highly flammable liquid and vapour.  
H226 : Flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistent bioaccumulative toxic  
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.