

Marker card - SK U/5,0 WH:UNBEDRUCKT - 0803922

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Marker card, Sheet, white, unlabeled, can be labeled with: Plotter, Office printing systems, Mounting type: Adhesive, Lettering field: 186 x 5 mm




Why buy this product

- Labeling service: Phoenix Contact can custom-label all TMT markers according to your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- Labeling service: Phoenix Contact can custom-label all TMT markers according to your requirements



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 007812
Weight per Piece (excluding packing)	15.26 g
Custom tariff number	39199000
Country of origin	Belgium
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	186 mm
Width (a)	5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 0 °C
Recommended storage conditions	20-25 °C / 40-50 % relative humidity.

General

Note	Print image may vary depending on laser printer
Color	white

Marker card - SK U/5,0 WH:UNBEDRUCKT - 0803922

Technical data

General

Components	free from silicone and halogen
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	630
Number of individual labels per row	18
Number of marker strips	35
Adhesive	Acrylic
Printability	Office printing systems
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	50 µm
Adhesive strength	20 µm
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

Marker card - SK U/5,0 WH:UNBEDRUCKT - 0803922

Classifications

ETIM

ETIM 5.0	EC000761
----------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Marker pen

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm