


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINDICHT® MR-M ATEX	29.11.2013

Enables the use of cable glands with smaller connection threads than the existing threaded holes
 With guide notch for O-ring
 Assembling with a wrench



Application range

Equipment group II / Category 2G+1D
 Devices, machines and apparatus
 For mobile applications in offshore and marine industries
 Chemical and petrochemical industry

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0028X
Material:	Body: nickel-plated brass O-ring: NBR
Temperature range:	-30°C to +90°C

Product Management	Document: LAPP_PRO1035EN.pdf	1 / 2
--------------------	------------------------------	-------



Part number	Thread/ male M1	Thread/ female M2	Overall height (mm)	Thread length/ D (mm)	Outer Ø (mm)
SKINDICHT® MR-M ATEX					
52104570	16 x 1.5	12 x 1.5	10.5	5.0	19.0
52104571	20 x 1.5	16 x 1.5	13.0	6.0	24,5
52104572	25 x 1.5	20 x 1.5	15.0	7.0	30,1
52104573	32 x 1.5	25 x 1.5	16.5	8.0	37,2
52104574	40 x 1.5	32 x 1.5	16.5	8.0	45,6
52104575	50 x 1.5	40 x 1.5	19.5	10.0	55,3
52104576	63 x 1.5	50 x 1.5	18.5	8.5	71,3