



# Deburring Blades

## N3 Light Duty Deburring Blade

RS Stock No. [244-6701](#)

	RS Code	244-6701			
	Pack Reference	BN3010			
	Cutting	Right Hand			
	Works best on	Internal and External Burrs			
	Used with Handle	NG-1, NG-3 + N Holder, Fine Burr			
Packed Weight and Dimensions					
Code	Pack Quantity	Weight g	Wmm	Hmm	Lmm
N3	10	13	32	5	63

	RS Code	244-6701
	Included Angle	50°
	Blade Material	HSS M2
	Blade Hardness	62 – 64 HRC
	L: Overall Length	22
	L1: Length Inside Handle	10
	L2: Protrusion from Handle Length	12
	L3: Min Cutting Width	2
	L4: Max Cutting Width	5
	D: Shank Diameter	2.6

### Instructions for successful deburring

Do not use heavy pressure when deburring as this will cause the blade to dig into the material and give an uneven finish. Use light and even pressure which will allow the blade and handle to work together to remove the burr and leave a smooth finish on the component

### Safety Information

Blades should be handled carefully as they are sharp and can cut. Blades can break causing flying objects. Sharp edges and flying objects can cause injury. Users and bystanders should wear protective safety glasses. Do not pry or bend blades. Keep blades and sharp tools away from children Do not grind blades as this will weaken the blade and cause breakage and possible injury