

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19160-0002](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 10-16 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19160](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 MolexKits Yes
 Overview [Splices](#)
 Product Name Closed-End Insulated
 UPC 800753110144

Physical

Barrel Type Closed
 Color - Resin Natural
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 1.041/g
 Packaging Type Bag
 Temperature Range - Operating 105°C
 Wire Insulation Diameter 9.65mm max.
 Wire Size AWG 10, 12, 14, 16

Electrical


Voltage - Maximum 600V

Material Info

Old Part Number NC-1610

Reference - Drawing Numbers

[Packaging Specification](#) PK-19408-109
[Product Specification](#) PS-19902-013
[Sales Drawing](#) SD-19160-001



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No**
**Low-Halogen Status
 Low-Halogen**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

19160Series

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	0640053500
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050600
Hand Crimp Tool	0640010600