

Warning label - PML-W200 (50X50)R - 0830452


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Warning label, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 50 x 50 mm



Key commercial data

| | |
|--------------------------------------|--|
| Packing unit | 1 pc |
| GTIN |  4 046356 717762 |
| Weight per Piece (excluding packing) | 99.99 g |
| Custom tariff number | 39199000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 50 mm |
| Width (a) | 50 mm |

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -40 °C ... 90 °C |
| Ambient temperature (assembly) | > 8 °C |
| Recommended storage conditions | 4 °C - 40 °C Storage in a cool and dark place in the original packaging is recommended. |

General

| | |
|-----------------------------|-----------------------------|
| Color | yellow |
| Type | Triangle |
| Components | Silicone-free |
| Material | PVC |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 500 |

Warning label - PML-W200 (50X50)R - 0830452

Technical data

General

| | |
|--|-------------------------------------|
| Number of individual labels per row | 1 |
| Adhesive | Acrylic |
| Printability | Thermal transfer |
| Device | 5146477 THERMOMARK ROLL |
| | 5146723 THERMOMARK ROLL X1 |
| | 5146257 THERMOMARK S1.1 |
| | 5146231 THERMOMARK X1.2 |
| Ink ribbon | 5145384 THERMOMARK-RIBBON 110 |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | Following DIN 50018:2013-05 |
| Climate level | AHT 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result | Test passed |
| Foil strength | 50 µm |
| Marking mounting type | Adhesive |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001694 |
| ETIM 4.0 | EC001777 |
| ETIM 5.0 | EC001777 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |

Warning label - PML-W200 (50X50)R - 0830452

Classifications

UNSPSC

| | |
|--------------|----------|
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |