

Sunday, 02 December 2012



www.sks-kontakt.de

News contact sitemap Login

main menu

- home
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
 - ▶ 0,64 mm system
 - ▶ 2 mm system
 - ▶ 4 mm system
 - ▶ 4 mm sliding sleeve system
 - ▶ 4 mm safety system
- oscilloscope test probes
- measuring leads
- plugs
- sockets
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ test probes ▶ test probes ▶ PRUEF 1

PRUEF 1

datasheet for PRUEF 1
article number: 931376101



[View Full-Size Image](#)

search online catalogue



Search

Messtermine

No events

Newsletter Anmeldung

Test & Measurement

QR-Code



| | |
|--|--|
| product description: | order number: 931 376-101 |
| description: | Miniature test probe for sampling extremely small measuring points. Shatter-proof grip, may be unscrewed. The stainless steel tip easily penetrates insulation and oxide layers. Solder connection up to 0.5 mm ² . |
| typ: | PRUEF 1 rot / red |
| system: | 2mm system |
| order number: | 931 376-101 |
| color | |
| other color versions: | |
| technical data | |
| measurement category acc. to IEC 61010: | CAT I |
| norm | IEC 61010 |
| pin dimensions | 1 mm |
| type of contact: | test tip (unsprung) |
| type of termination: | solder |
| rated voltage: | 30 VAC / 60 VDC |
| rated current: | 1 A |
| Please consider derating curve! | |
| contact resistance: | 50 mOhm |
| material | |
| contact material: | tip: stainless steel contact part: brass |
| contact surface material: | nickel |
| housing material: | PVC - P |
| environmental conditions: | |
| temperature range: | -25 °C to +60 °C |
| drawing | |

