

Fuseholder Open Design, 6.3 x 32 mm, Solder



250 V · 16 A (UL)



**Description**

- Screw or rivet fastening

**Standards**

- UL 512  
- CSA C22.2 no. 39


**Approvals**

- UL File Number: E39328  
- CSA File Number: 38456

**Weblinks**


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

**Technical Data**

Fuse-Link	6.3 x 32mm
Mounting	Screw or Rivet
Terminal	Solder
Rated Voltage	250V (CSA), VAC (UL)
Rated current	10A (CSA) 16A (UL)
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Socket	Thermoset, black, UL 94V-0
Material: Terminals	Nickel-Silver
Unit Weight	7.27 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 Rated voltage, Rated current, Approvals

Soldering Methods	Iron
Solderability	350 °C / 2 sec acc. to IEC 60068-2-20, Test Ta, method 2
Resistance to Soldering Heat	350 °C / 10 sec acc. to IEC 60068-2-20, Test Tb, method 2
Contact Resistance	< 5mΩ at 20 mV
Dielectric Strength	> 3kV (50Hz; 1 min)
Impulse Withstand Voltage	> 4kV between Life parts
Insulation Resistance	> 10MΩ between Life parts (500VDC; 1 min)


**Dimension**



Variant 0031.6001

Variant 0031.6010

Derating Curves



All Variants

Holder	Strip	Order Number
●		0031.6001
	●	0031.6010

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging Unit** Bulk (100 pcs.)