



KLINGER graphite SLN

Pure exfoliated graphite with a Nickel foil reinforcement for improved handling and load-bearing characteristics. The excellent conformability of graphite means that the material is suitable for applications where bolt load is limited or flanges are damaged.

The Klinger group has been recognised as the market leader in gaskets and sealing for over a century. Our research and development laboratories have investigated over 250 different fibre forms in the search for asbestos free alternatives. The search has resulted in a range of high quality and high performance asbestos free materials that have been proven in service

General Properties

- Excellent resistance to steam
- Improved handling due to 0.013mm Nickel insert
- Resistant to virtually all media
- Outstanding resistance to high and low temperature
- High compressibility
- Good leakage properties
- Unlimited storage life
- Anti-stick finish on both sides
- Easy to cut

Tests and Certifications

- WRc Approval
- DIN DVGW NG-5124AT0417
- Firesafe according to BS 5146

Availability

- Sheeting (m): 1.0 x 1.0
- Thickness (mm): 0.45, 0.8, 1.0, 1.5, 2.0, 3.0


Also available in 99.85% pure nuclear grade



Certificate No. FM 10571



KLINGERgraphite SLN



Application Guidelines

1. Usually satisfactory without reference.
2. Usually satisfactory, but suggest you refer to Klinger for advice
3. Caution: May be suitable but essential that you refer to Klinger for advice.

Chemical compatibility must be considered in all cases.

Typical Specifications

Compressibility ASTM F 36 A		40%
Recovery ASTM F 36 A		15%
Stress relaxation DIN 52913	50MPa, 16h/300°C	min 48MPa
Klinger cold/hot compression (50MPa)	Thickness decrease 23°C decrease at 300°C	40% 1.5%
Gas leakage according to DIN 3535/6		<0.5ml/min
Chlorides (soluble)		<40ppm
Fluoride and Chloride Content		<200ppm
Density of Graphite		1.0g/cm ³
Purity		min 98%

Typical values for 1.5mm thick material

Head Office

KLINGER Ltd
Wharfedale Road
Euroway Trading Estate
Bradford BD4 6SG

Tel: 01274 688 222
Fax: 01274 688 549

Klinger Ltd. Grangemouth

Tel: 01324 472 231
Fax: 01324 482 111

Klinger Ltd. Aberdeen

Tel: 01224 772 962
Fax: 01224 772 953

Klinger Ltd. Middlesbrough

Tel: 01642 220 289
Fax: 01642 220 290

Klinger Ltd. Runcorn

Tel: 01928 577 030
Fax: 01928 575 223

Klinger Ltd. International

Tel: 020 8308 0100
Fax: 020 8308 0200

All information and recommendations contained in this specification sheet are to the best of our knowledge correct. Since conditions of use are beyond our control, users must satisfy themselves that the products are suitable for the intended processes and uses. No warranty is given or implied in respect of information or recommendations or that any use of products will not infringe rights belonging to other parties. In any event or occurrence our liability is limited to our invoice value of the goods delivered by us to you. We reserve the right to change product design and properties without notice