



### Main

Product or component type	Earth leakage add-on block
Device short name	Vigi iC60
Poles description	1P + N
Neutral position	Left
[In] rated current	63 A
Network type	AC
Network frequency	50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz conforming to IEC 61009-1 230 V AC 50/60 Hz conforming to EN 61009-1
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Class AC
9 mm pitches	4

### Complementary

Device location in system	Outgoer
Overvoltage protection	Without
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
Comb busbar distribution block compatibility	Bottom: YES
Height	91 mm
Width	54 mm
Depth	73.5 mm
Product weight	0.165 kg
Colour	White
Connections - terminals	Tunnel type terminal downside 1 cable(s) 1...25 mm <sup>2</sup> flexible with cable end Tunnel type terminal downside 1 cable(s) 1...25 mm <sup>2</sup> flexible without cable end Tunnel type terminal downside 1 cable(s) 1...35 mm <sup>2</sup> rigid without cable end
Wire stripping length	14 mm (bottom)
Tightening torque	3.5 N.m (bottom)
Product compatibility	Single terminal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN 61009-1 IEC 61009-1
IP degree of protection	IP20
Pollution degree	3 conforming to IEC 60947-2
Electromagnetic compatibility	8/20 $\mu$ s impulse withstand 250 A conforming to IEC 61009-1
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1001 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Period	18 months
--------	-----------