

## General Information

<b>Extended Product Type:</b>	SU202PR-K10
<b>Product ID:</b>	2CDS272327R0427
<b>EAN:</b>	4016779848237
<b>Catalog Description:</b>	Miniature Circuit Breaker - SU200PR - 2P - K - 10 A
<b>Long Description:</b>	SU202PR-K10 MCB K-Char., 10kA, 10A, 2P, RTT UL 489, Ring Cable Lug

## Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Miniature Circuit Breakers MCBs

## Ordering

<b>EAN:</b>	4016779848237
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85362010

## Dimensions

<b>Product Net Width:</b>	35 mm
<b>Product Net Depth:</b>	71 mm
<b>Product Net Height:</b>	115 mm
<b>Product Net Weight:</b>	0.28 kg

## Container Information

<b>Package Level 1 Units:</b>	5 piece
<b>Package Level 1 Width:</b>	121 mm
<b>Package Level 1 Length:</b>	191 mm
<b>Package Level 1 Height:</b>	82 mm
<b>Package Level 1 Gross Weight:</b>	1.45 kg
<b>Package Level 1 EAN:</b>	4016779850230

## Environmental

<b>Ambient Air Temperature:</b>	Operation -25 ... +55 °C Storage -40 ... +70 °C
<b>Resistance to Shock acc. to IEC 60068-2-27:</b>	25g / 2 shocks / 13 ms
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
<b>Environmental Conditions:</b>	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %

## Technical

<b>Standards:</b>	IEC/EN 60947-2 UL 489 CSA 22.2 No. 5
<b>Number of Poles:</b>	2
<b>Tripping Characteristic:</b>	K
<b>Rated Current (I<sub>n</sub>):</b>	10 A
<b>Rated Operational Voltage:</b>	acc. to IEC60947-2 400 V AC
<b>Power Loss:</b>	3.64 W per Pole 1.82 W
<b>Rated Insulation Voltage (U<sub>i</sub>):</b>	acc. to IEC/EN 60664-1 440 V
<b>Operational Voltage:</b>	Maximum (Incl. Tolerance) 440 V AC Minimum 12 V AC
<b>Rated Frequency (f):</b>	50 Hz 60 Hz
<b>Rated Ultimate Short-Circuit Breaking Capacity (I<sub>cu</sub>):</b>	15 kA
<b>Rated Service Short-Circuit Breaking Capacity (I<sub>cs</sub>):</b>	11.2 kA
<b>Energy Limiting Class:</b>	3
<b>Overvoltage Category:</b>	III
<b>Pollution Degree:</b>	2
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	4 kV (6.2 kV @ sea level) (5.0 kV @ 2000 m)
<b>Dielectric Test Voltage:</b>	50 / 60 Hz, 1 min: 2 kV

<b>Housing Material:</b>	Insulation Group I, RAL 7035
<b>Actuator Type:</b>	Insulation group II, black, sealable
<b>Contact Position Indication:</b>	Red ON / Green OFF
<b>Degree of Protection:</b>	IP20
<b>Remarks:</b>	IP40 in enclosure with cover
<b>Electrical Endurance:</b>	20000 AC cycle
<b>Mechanical Endurance:</b>	20000 cycle
<b>Terminal Type:</b>	Ring-Tongue Terminals
<b>Screw Terminal Type:</b>	Ring-Tongue Terminal with Captive Screw
<b>Tightening Torque:</b>	2.8 N·m
<b>Recommended Screw Driver:</b>	Pozidriv 2
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Mounting Position:</b>	Any

### Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	480Y / 277 V AC
<b>Connecting Capacity UL/CSA:</b>	Conductor 18 ... 4 AWG
<b>Tightening Torque UL/CSA:</b>	25 in·lb
<b>Short-Circuit Current Rating (SCCR):</b>	10 kA

### Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	2CDK400587D2701
--	-----------------

### Classifications

<b>eClass:</b>	7.0 27141901
<b>ETIM 4.0:</b>	EC000042 - Miniature circuit breaker (MCB)
<b>ETIM 5.0:</b>	EC000042 - Miniature circuit breaker (MCB)
<b>Object Classification Code:</b>	F
<b>UNSPSC:</b>	39121614

### Accessories

5 Products				Filter	<input type="text"/>
Identifier	Type	Description	Qty	Unit Of Measure	
<a href="#">2CDS200908R0001</a>	S2C-A1U	S2C-A1U - Accessory for Miniature Circuit Breakers	1	piece	
<a href="#">2CDS200908R0002</a>	S2C-A2U	S2C-A2U - Accessory for Miniature Circuit Breakers	1	piece	
<a href="#">2CDS200914R0001</a>	S2C-H6RU	S2C-H6RU - Accessory for Miniature Circuit Breakers	1	piece	
<a href="#">2CDS200917R0001</a>	S2C-TC20U	S2C-TC20U - Mechanical Accessories	1	piece	
<a href="#">2CDS200924R0001</a>	S2C-S6RU	S2C-S6RU - Accessory for Miniature Circuit Breakers	1	piece	

