



# H48-6 INTERFACE MATERIAL

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830  
Date of issue: 10/12/2015 Revision date: 3/3/2019 Version: 1.3

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name : H48-6 INTERFACE MATERIAL  
Product code : H48-6  
Type of product : Thermal interface material, Fillers, putties, plasters, modelling clay

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use  
Use of the substance/mixture : Conductive agents  
Fillers  
Function or use category : Fillers, Conductive agents

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

##### Supplier

##### UK

RS Components Ltd  
Birchington Road  
Corby  
Northants  
NN17 9RS  
Tel: +44 (0) 845 850 9900  
Email: [RCustomerServicesUK@rs-components.com](mailto:RCustomerServicesUK@rs-components.com)  
Website: [www.rs-online.com](http://www.rs-online.com)

##### Ireland

RS Components Ltd  
Glenview Industrial Estate  
Herberton Road  
Rialto  
Dublin 12  
Tel: +353 (0) 1 415 3100  
Email: [Enquiries.ie@rs-components.com](mailto:Enquiries.ie@rs-components.com)  
Website: [www.rs-online.com](http://www.rs-online.com)

#### 1.4. Emergency telephone number

Emergency number : +44 1865 407 333 (24hr)

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

##### Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

No labelling applicable

#### 2.3. Other hazards

No additional information available

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable

# H48-6 INTERFACE MATERIAL

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
SILICONE	(CAS-No.) 68083-18-1 (EC-No.) 614-273-4	80	Not classified
ALUMINA	(CAS-No.) 1344-28-1 (EC-No.) 215-691-6	20	Not classified

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.  
First-aid measures after skin contact : Wash skin with plenty of water.  
First-aid measures after eye contact : Rinse eyes with water as a precaution.  
First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/effects after inhalation : Inhalation may cause irritation (cough, short breathing, difficulty in breathing).  
Symptoms/effects after skin contact : Causes mild skin irritation.  
Symptoms/effects after eye contact : mild eye irritation.  
Symptoms/effects after ingestion : Ingestion may cause nausea and vomiting. May cause irritation to the digestive tract.

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

- Suitable extinguishing media : Water spray. Dry powder. Foam.

### 5.2. Special hazards arising from the substance or mixture

- Hazardous decomposition products in case of fire : Toxic fumes may be released.

### 5.3. Advice for firefighters

- Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

- Emergency procedures : Ventilate spillage area.

#### 6.1.2. For emergency responders

- Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

### 6.2. Environmental precautions

Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Mechanically recover the product.  
Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

- Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

### 7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Store in a well-ventilated place. Keep cool.

### 7.3. Specific end use(s)

No additional information available

# H48-6 INTERFACE MATERIAL

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

##### ALUMINA (1344-28-1)

Germany	TRGS 910 Acceptable concentration notes	
United Kingdom	Local name	Aluminium oxides
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	4 mg/m <sup>3</sup> respirable dust 10 mg/m <sup>3</sup> inhalable dust
United Kingdom	Regulatory reference	EH40/2005 (Third edition, 2018). HSE

#### 8.2. Exposure controls

##### Appropriate engineering controls:

Ensure good ventilation of the work station. Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure.

##### Personal protective equipment:

Protective clothing. Safety glasses. Gloves.

##### Hand protection:

Protective gloves

##### Eye protection:

Safety glasses

##### Skin and body protection:

Wear suitable protective clothing

##### Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

##### Personal protective equipment symbol(s):



##### Environmental exposure controls:

Avoid release to the environment.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

Physical state	: Solid
Colour	: Grey.
Odour	: odourless.
Odour threshold	: No data available
pH	: Approx. 7
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: Not applicable
Boiling point	: > 35 °C
Flash point	: > 93 °C
Auto-ignition temperature	: Not applicable
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: >2
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

# H48-6 INTERFACE MATERIAL

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Explosive properties : No data available  
Oxidising properties : No data available  
Explosive limits : Not applicable

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified  
Acute toxicity (dermal) : Not classified  
Acute toxicity (inhalation) : Not classified  
Skin corrosion/irritation : Not classified  
pH: Approx. 7  
Serious eye damage/irritation : Not classified  
pH: Approx. 7  
Respiratory or skin sensitisation : Not classified  
Germ cell mutagenicity : Not classified  
Carcinogenicity : Not classified  
Reproductive toxicity : Not classified  
STOT-single exposure : Not classified  
STOT-repeated exposure : Not classified  
Aspiration hazard : Not classified

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.  
Acute aquatic toxicity : Not classified  
Chronic aquatic toxicity : Not classified

### 12.2. Persistence and degradability

#### ALUMINA (1344-28-1)

Persistence and degradability	Not established.
-------------------------------	------------------

### 12.3. Bioaccumulative potential

#### ALUMINA (1344-28-1)

Bioaccumulative potential	No bioaccumulation data available.
---------------------------	------------------------------------

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

No additional information available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

# H48-6 INTERFACE MATERIAL

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.2. UN proper shipping name</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.3. Transport hazard class(es)</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.4. Packing group</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.5. Environmental hazards</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated

No supplementary information available

### 14.6. Special precautions for user

#### Overland transport

Not regulated

#### Transport by sea

Not regulated

#### Air transport

Not regulated

#### Inland waterway transport

Not regulated

#### Rail transport

Not regulated

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

##### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to REGULATION (EU) No 649/2012 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 4 July 2012 concerning the export and import of hazardous chemicals.

Substance(s) are not subject to Regulation (EC) No 850/2004 of the European Parliament and of the Council of 29 April 2004 on persistent organic pollutants and amending Directive 79/117/EEC.

##### 15.1.2. National regulations

No additional information available

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

### SECTION 16: Other information

No additional information available

SDS EU (REACH Annex II)

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*