

6GK5204-2BC10-2AA3 SCALANCE X204-2LD

Technical Data

Product-type designation



SCALANCE X204-2LD

SCALANCE X204-2LD, MANAGED IE SWITCH, 4 X 10/100MBIT/S RJ45 PORTS, 2 X 100MBIT/S SINGLEMODE BFOC, ERROR SIGNAL CONTACT WITH SET BUTTON, REDUNDANT POWER SUPPLY,PROFINET-IO DEVICE, NETWORK MANAGEMENT, INTEGRATED REDUNDANCY MANAGER AND ELECTRONIC MANUAL ON CD, C-PLUG OPTIONAL

Transmission rate

Transfer rate / 1	10 Mbit/s
Transfer rate / 2	100 Mbit/s

Interfaces

Number of electrical/optical connections	
<ul style="list-style-type: none"> for network components or terminal equipment / maximum 	6
Number of electrical connections	
<ul style="list-style-type: none"> for network components and terminal equipment 	4
<ul style="list-style-type: none"> for alarm contact 	1
<ul style="list-style-type: none"> for power supply 	1
<ul style="list-style-type: none"> for redundant power supply 	1
Design of electrical connection	
<ul style="list-style-type: none"> for network components and terminal equipment 	RJ45 port
<ul style="list-style-type: none"> for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> for power supply 	4-pole terminal block
Number of optical interfaces / for optical waveguide / at 100 Mbit/s	2
Design of optical interface / for optical waveguide / at 100 Mbit/s	BFOC port (singlemode up to 26 km)
Connectable optical power relative to 1 mW	
<ul style="list-style-type: none"> of the transmitter output 	-15...-7 dB

Optical sensitivity relative to 1 mW / of the receiver input / minimum	-34 dB
Attenuation / of fiber-optic cable transmission link / minimum necessary	0 dB
Range / at the optical interface / depending on the optical fiber used	0...26 km
design of the removable storage / C-PLUG	Yes
Inputs/outputs	
Operating voltage / of signaling contacts / at DC / rated value	24 V
Operating current / of signaling contacts / at DC / maximum	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of supply voltage	DC
Supply voltage / external	24 V
• minimum	18 V
• maximum	32 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.265 A
Active power loss / at 24 V / for DC	6.36 W
Permitted ambient conditions	
Ambient temperature	
• during operating	-40...+60 °C
• during storage	-40...+70 °C
• during transport	-40...+70 °C
Relative humidity / at 25 °C / without condensation / during operating / maximum	95 %
Protection class IP	IP30
Design, dimensions and weight	
Design	compact
Width	60 mm
Height	125 mm
Depth	124 mm
Net weight	0.78 kg
Type of mounting	
• 35 mm DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
Product properties, functions, components / general	
Cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	50
Cascading in cases of star structuring	Any (depending only on signal propagation time)
Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes

• Port mirroring	Yes
• for IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• DCP	Yes
• LLDP	Yes
Identification & maintenance	
• I&M0 - device-specific information	Yes
• I&M1 - plant identification/location name	Yes
Product functions / Diagnosis	
Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
Product functions / DHCP	
Product function / DHCP client	Yes
Product functions / Redundancy	
Product function	
• Ring redundancy	Yes
• Redundancy manager	Yes
• Standby redundancy	No
• HSR redundancy protocol	Yes
• MRP redundancy protocol	Yes
• redundancy procedure PRP	No
• Passive listening	Yes
Protocol / is supported / PRP	Yes
Product functions / Security	
Protocol / is supported / SSH	Yes
Product functions / Time	
Product function / SICLOCK support	Yes
Protocol / is supported	
• NTP	No
• SNTP	Yes
Standards, specifications, approvals	
Standard	
• for EMC / from FM	FM3611: Class 1, Division 2, Group A,

<ul style="list-style-type: none"> • for hazardous zone 	B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> • for safety / of CSA and UL 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • for hazardous area / of CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> • for emitted interference 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-4 (Class A)
Verification of suitability	EN 61000-6-2
<ul style="list-style-type: none"> • CE mark 	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • Railway application in accordance with EN 50155 	Yes
<ul style="list-style-type: none"> • Railway application in accordance with EN 50124-1 	No
Marine classification association	No
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	Yes
<ul style="list-style-type: none"> • Bureau Veritas (BV) 	Yes
<ul style="list-style-type: none"> • Det Norske Veritas (DNV) 	Yes
<ul style="list-style-type: none"> • Germanische Lloyd (GL) 	Yes
<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) 	Yes
<ul style="list-style-type: none"> • Nippon Kaiji Kyokai (NK) 	Yes
<ul style="list-style-type: none"> • Polski Rejestr Statkow (PRS) 	Yes
letzte Änderung:	May 14, 2012