

CP1956 v1.2 RS 908-2777

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 1

Compilation date: 02/08/2017

Revision No: 2

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: S74 FLANGE SEALANT

Product code: RS908-2777

Synonyms: 574

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: RS Components Ltd	RS Components Ltd
Birchington Road	Glenview Industrial Estate
Corby	Herberton Road
Northamptonshire	Rialto
NN17 9RS England	Dublin 12

Tel: +44 (0) 1536 40288

(01) 415 31238

Email: RCustomerServicesUK@rs-components.comenquiries.ie@rs-components.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 1536 402888 (8am to 8pm)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Acute 1: H400; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Sens. 1: H317

Most important adverse effects: May cause an allergic skin reaction. Causes serious eye irritation. Very toxic to aquatic life. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H400: Very toxic to aquatic life.

H411: Toxic to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental



[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 2

Signal words: Warning**Precautionary statements:** P261: Avoid breathing vapours.

P264: Wash hands thoroughly after handling.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+352: IF ON SKIN: Wash with plenty of water/soap.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P321: Specific treatment (see instructions on this label).

2.3. Other hazards**PBT:** This product is not identified as a PBT/vPvB substance.**Section 3: Composition/information on ingredients****3.2. Mixtures****Hazardous ingredients:**

BIS(ISOPROPYL)NAPHTHALENE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
254-052-6	38640-62-9	-	Aquatic Acute 1: H400; Aquatic Chronic 2: H411	10-30%

POLYGLYCOL DIMETHACRYLATE

203-652-6	109-16-0	-	Skin Sens. 1: H317	10-30%
-----------	----------	---	--------------------	--------

HYDROXYALKYL METHACRYLATE

248-666-3	27813-02-1	-	STOT SE 3: H335; Eye Irrit. 2: H319; Skin Sens. 1: H317	1-10%
-----------	------------	---	---	-------

CUMENE HYDROPEROXIDE

201-254-7	80-15-9	-	Org. Perox. EF: H242; Acute Tox. 3: H331; Acute Tox. 4: H312; Acute Tox. 4: H302; STOT RE 2: H373; Skin Corr. 1B: H314	1-10%
-----------	---------	---	--	-------

N,N-DIMETHYL-P-TOLUIDINE

202-805-4	99-97-8	-	Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Aquatic Chronic 3: H412	<1%
-----------	---------	---	--	-----

Section 4: First aid measures**4.1. Description of first aid measures****Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.**Ingestion:** Wash out mouth with water. Consult a doctor.

[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 3

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures**5.1. Extinguishing media**

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 4

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Orange

Odour: Barely perceptible odour

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Insoluble

Viscosity: No data available.

Boiling point/range°C: >35

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: >93

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: No data available.

Relative density: 1.1

[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 5

pH: No data available.

VOC g/l: 48.6

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

CUMENE HYDROPEROXIDE

ORL	MUS	LDLO	5	gm/kg
ORL	RAT	LD50	382	mg/kg
SCU	RAT	LD50	382	mg/kg

N,N-DIMETHYL-P-TOLUIDINE

IPR	MUS	LD50	212	mg/kg
-----	-----	------	-----	-------

Relevant hazards for product:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated

[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 6

Respiratory/skin sensitisation	DRM	Hazardous: calculated
--------------------------------	-----	-----------------------

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information**12.1. Toxicity**

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations**13.1. Waste treatment methods**

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information**14.1. UN number**

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.

[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 7

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment**Section 16: Other information****Other information**

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H242: Heating may cause a fire.

H301: Toxic if swallowed.

H302: Harmful if swallowed.

H311: Toxic in contact with skin.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H335: May cause respiratory irritation.

H373: May cause damage to organs <or state all organs affected, if known> through prolonged or repeated exposure <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H400: Very toxic to aquatic life.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

[cont...]

SAFETY DATA SHEET

S74 FLANGE SEALANT

Page: 8

and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.