



Product Information

LINEA light

5925UAP100L51 RAL9002

5925UAP100S70 M10x15 (Supplied with M10x15/10 Threaded Stem)

EAN 4031582348934

Swivel castor with wheel brake, housing made of Polyamide. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing, with blind hole for furniture fittings

Technical Data

Wheel diameter	100 mm
Width of Tread	20 mm
Castor width	73 mm
Centre hole	11 mm
Offset	32 mm
Swivel Interference	180 mm
Overall height	100 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Load capacity	100 kg
Load capacity (static)	200 kg



Roll performance + + + + +

Movement noise + + + + +

Attrition + + + + +

Corrosion resistance + + + + +

