



Figure similar

Ordering data

6SL3211-0AB21-1UA1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Input

Number of phases	1 AC
Line voltage	200 ... 240 V ±10 %
Line frequency	47 ... 63 Hz
Rated current	14.70 A

Output

Number of phases	3 AC
Rated power	1.10 kW
Rated current (IN)	6.00 A
Pulse frequency	8 kHz
Output frequency for V/f control	0 ... 650 Hz
As a result of legal stipulations, a limit to 550 Hz is in production	

General tech. specifications

Offset factor $\cos \varphi$	0.95
------------------------------	------

Communication

Communication	RS485
---------------	-------

Mechanical data

Degree of protection	IP20
Size	FSB
Net weight	1.40 kg
Width	140.0 mm
Height	160.0 mm
Depth	142.0 mm

Ambient conditions

Installation altitude	1000 m
-----------------------	--------

Ambient temperature

Operation	-10 ... 40 °C
Storage	-40 ... 70 °C

Relative humidity

Max. operation	95 % Condensation not permissible
----------------	-----------------------------------

Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
---	-----

Standards

Compliance with standards	UL, cUL, CE, C-Tick (RCM)
CE marking	Low-voltage directive 2006/95/EC

Inputs/ outputs

Digital inputs

Number	3
--------	---

Analog inputs

Number	1 (?PMD_AAC002_001_000 ?)
--------	---------------------------

Digital outputs

Number	1 (Isolated optocoupler output, NPN type)
--------	---