



Licron Crystal ESD-Safe Coating

1756

Techspray's ESD-safe products can help maintain work areas within the ANSI/ESDS20.20 standards set by the ESD Association (www.esda.com). In a static-free environment, the work area, tools and personnel form a circuit (see diagram to right). Electrostatic Discharge (ESD) occurs when the charges of two surfaces with a large electronic potential (difference) equalize instantaneously. The resulting discharge or spark can cause catastrophic or latent damage to electronic components. ESD programs maintain an equal potential by maintaining continuous contact with ground, avoiding ESD damage. Cleaners, lotions, and coatings are an integral part of an ESD control program.



Permanent, clear ESD-safe coating

Versatile, crystal clear urethane coating that adheres to metal, plastic, and most other surfaces. Ideal for converting standard bumpers, bins, tools, and surfaces to ESDsafe, saving expensive replacement cost. The end result is compliant with ANSI/ESDS20.20, which prevents static damage to sensitive electronic components.

- Rugged static dissipative coating
- Surface Resistivity of 10^6 To 10^9 ohms
- Non-ozone depleting
- Operating temperature range up to 302°F (155°C)
- Humidity independent

Product Packaging

1756-8S
Licron ESD-Safe Coating
8 oz
12 units/case





Instructions

Licron Crystal can be sprayed using standard spray guns or paint systems (test compatibility on seals and other plastic or rubber components). A grounding wire can then be attached (i.e. by conductive adhesive) similar to an ESD floor.

Technical Information

Chemical & Physical Properties

Appearance	Dark blue liquid
Odor	Alcohol odor
Flash Point	22.2°C (72°F)
VOC (EPA)	57%
Boiling Point	80°C (176°F)
Density	0.91 - 0.94

Chemical Composition

CHEMICAL NAME	CAS #
2-Propanol	67-63-0
1-Butanol	71-36-3
Polymer, Proprietary	
Nitromethane	75-52-5
Methanol	67-56-1
Propane	74-98-6
N-Butane	106-97-8
Includes other hazardous components in non-reportable quantities	

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.



Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW