

Datasheet

Stock No: 121-7815, 121-7816, 121-7817, 121-7818, 121-7819

RS Pro 3PCO Miniature Power Relay




Specifications:

- 3 Pole 10A Industrial Plug-in Relay
- Gold plated contact
- Double side LED integrated in relay
- Lockable test button and inspection window
- Identification of coils through test button colour (AC red / DC blue)
- Conformity with RoHs directive

RS Stock No		121-7815	121-7816	121-7817	121-7818	121-7819
Characteristics						
Nominal Voltage		12VDC	24VDC	24VAC	110VAC	230VAC
Options		LED + Test Button + Diode	LED + Test Button + Diode	LED + Test Button	LED + Test Button	LED + Test Button
Contact	Configuration	3 Pole Change Over				
	Rated Current AC-1	10A/250VAC, 30Vdc				
	Rated Voltage AC-15	1/3HP, 120VAC, 1/2HP, 240VAC				
	Switching Capacity (resistive)	2500VA, 300W				
	Initial Contact Resistance	≤50mΩ				
	Material	Ag alloy				
	Electrical Durability	≥10 ⁵ times (1800 Ops/h)				
	Mechanical Durability	≥10 ⁷ times (18000 Ops/h)				
Pick-up Voltage (23°C)		DC: ≤75% rated voltage, AC: ≤80% rated voltage				
Drop-out Voltage (23°C)		DC: ≥10% rated voltage, AC: ≥30% rated voltage				
Maximum Voltage (23°C)		110% rated voltage				
Insulation resistance		≥500mΩ (500VDC)				
Coil Operating Power	DC (W)	1.4				
	AC (VA)	2				
Operating Time (at nominal voltage)		≤20ms				
Release Time (at nominal voltage)		≤20ms				
Initial Breakdown Voltage	Between open contacts	1000VAC/1min				
	Between Poles	2000VAC/1min				
	Between contacts and coil	2000VAC/1min				
Ambient Temperature		-25~+55°C				
Humidity		35%~85%RH				
Air Pressure		86~106KPa				
Shock Resisance		10G				
Vibration Resistance		10~55Hz double-amplitude: 1.0mm				
Mounting		Plug-in				
Unit Weight		50g				

Mounting Dimensions (mm)



Schemes

