

Specification @ 20°C:

Application: single ended amplifier with EL84 valve
Output: 3W

Inductance (6 - 10): 6H (typ.) @ 1000Hz, 1V
Leakage inductance @ 1kHz, 0.1V: 14mH (typ.)
Interwinding capacitance @ 10kHz: 725pF (typ.)


DC resistance (+/-15%):
(6 - 10): 365
(14 - 12): 0.90

Maximum DC in primary: 45mA

Hi-pot, primary to secondary: 2kVRMS for 2 seconds

Mass: 0.465kg

All dimensions +/- 0.3mm unless stated otherwise



Unit 5, Oxonian Park, Langford Locks,
Kidlington, Oxfordshire. OX5 1FP
Tel: (01865) 885085 Fax: (01865) 855075
Website: www.oep.co.uk

| DESCRIPTION | ISSUE | DATE | DRAWN | CHECKED |
|--|-------|----------|-------|---------|
| 5k to 8 / 16 single ended output transformer | 1 | 23/03/16 | CS | |
| | 2 | 25/05/16 | CS | |
| | | | | |

DRAWING NUMBER

R35A03F/4

Scale: 1 to 1

All dimensions in mm unless stated otherwise