




ENGLISH

Datasheet

2 Output Toroidal Transformer, 225VA, 25 V ac

RS Stock number [671-9173](#)

Open Style, with leads, 2x115V Primary, 225VA



RS Code No.	RS Part No.	Full Load Vsec [V]	Rated Current per Sec [A]	No Load Vsec [V]	DC resistance [Ohms] @ 25° C
671-9167	81598-P2S2	2x12	9.375	2 x 13.07	2 x 0.0515
671-9176	81599-P2S2	2x15	7.500	2 x 16.22	2 x 0.0791
671-9179	81600-P2S2	2x18	6.250	2 x 19.39	2 x 0.1062
671-9173	81601-P2S2	2x25	4.500	2 x 27.12	2 x 0.2155
671-9182	81602-P2S2	2x30	3.750	2 x 32.44	2 x 0.3287
671-9185	81603-P2S2	2x55	2.045	2 x 59.32	2 x 1.0408

Primary Winding

Input Voltage : 2 x 115V±10% @ 50/60Hz
DC Resistance @25°C = 2 x 4.0 Ohms (approx)
Magnetising Current @ 115V = 350.0mA (approx)
Magnetising Current @ 126.5V = 700.0mA (approx)

Losses

Iron Losses 9.00 Watts (approx)
Copper Losses 27.0 Watts approx

Temperature Class

Winding Wire (Primary & Secondary). Class H (180° C)
Insulation between input and output. Class B (130° C)
Connection lead insulation. Class A (105° C)

Standards

Designed,manufactured and tested according to the requirements of:
EN61558 Class II, Non-Short-Circuit Proof
VDE0570 Class II
IEC61558 Class II
UL506

Physical Data

Approximation Dimension Diameter 120mm*
Height 50mm
Approximate weight 2.290 Kg
* Measured away from leadout bulge, allow extra 4mm at leads

Terminations

Primary Solid Copper Conductors (Extension of winding wire) double Insulated over their entire length with PVC tubing 150mm Long, with 10mm tinned ends.
Secondary Solid copper conductors (extension of winding wire) insulated over their entire length with PVC tubing 150mm Long, with 10mm tinned ends.