

Professionally approved products.

Datasheet

RS Lithium Thionyl Chloride D Battery

RS Stock 778-1125



Benefits

- High voltage response, stable during most of the lifetime of the application
- Wide operating temperature range (60°C/+85°C)
- Low self-discharge rate (less than 1 % after 1 year of storage at + 20°C)
- Easy integration into compact systems
- Superior resistance to atmospheric corrosion

Key features

- Stainless steel container and end caps (low magnetic signature)
- Hermetic glass-to-metal sealing
- Non-flammable electrolyte
- Underwriters Laboratories (UL) Component Recognition
- Compliant with IEC 60086-4 safety standard and IEC 60079-11 intrinsic safety standard
- Restricted for transport (Class 9)

Main applications

- Utility metering
- Automatic meter readers
- Buoys
- Measuring equipment
- Industrial applications
- Professional electronics

Electrical characteristics

(typical values relative to cells stored for one year or less at + 30°C max.)

| | |
|---|--------------------------------|
| Nominal capacity <i>(at 4 mA +20°C 2.0 V cut-off. The capacity restored by the cell varies according to current drain, temperature and cut-off)</i> | 7.7 Ah |
| Open circuit voltage (at +20°C) | 3.67 V |
| Nominal voltage (at 0.5 mA + 20°C) | 3.6 V |
| Nominal energy | 27.72 Wh |
| Pulse capability: Typically up to 300 mA <i>(300 mA/0.1 second pulses, drained every 2 mn at +20°C from undischarged cells with 10 µA base current, yield voltage readings above 3.0 V. The readings may vary according to the pulse characteristics, the temperature, and the cell's previous history. Fitting the cell with a capacitor may be recommended in severe conditions. Consult Saft)</i> | |
| Maximum recommended continuous current <i>(Higher currents possible, consult Saft)</i> | 150 mA |
| Storage <i>(recommended)</i> <i>(for more severe conditions, consult Saft)</i> | +30°C (+86°F) max |
| Operating temperature range <i>(Operation above ambient T may lead to reduced capacity and lower voltage readings at the beginning of pulses. Consult Saft)</i> | - 60°C/+85°C (-76°F/+185°F) |

Physical characteristics

| | |
|------------------------------|--|
| Diameter (max) | 26.0 mm (1.02 in) |
| Height (max) | 49.1 mm or 50.4 mm (1.93 in or 1.98 in) depending on finish type |
| Typical weight | 48 g (1.7 oz) |
| Li metal content | approx. 2.0 g |
| Available termination suffix | |
| CNR | radial tabs |
| 3 PF, 3 PF RP | radial pins |
| CNA (AX) | axial leads |
| FL | flying leads... etc. |

