

Product description

Preset for PROFINET mode!

SCALANCE XB208 managed Layer 2 IE Switch 8x 10/100 Mbit/s RJ45 ports 1x console port; Diagnostics LEDs Redundant power supply temp. range 0 °C to +60 °C; mounting onto standard rail; Default PROFINET



Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s
---------------	-----------------------

Interfaces / for communication / integrated

Number of electrical connections	8; RJ45
<ul style="list-style-type: none"> for network components or terminal equipment 	

Interfaces / others

Number of electrical connections	
<ul style="list-style-type: none"> for operator console for management purposes for power supply for redundant voltage supply 	<p>1</p> <p>1</p> <p>1</p> <p>1</p>

Type of electrical connection

<ul style="list-style-type: none"> for operator console for management purposes for power supply 	<p>RJ11</p> <p>RJ45</p> <p>6-pole terminal block</p>
---	--

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
---	----

Supply voltage	
<ul style="list-style-type: none"> external 	24 V
<ul style="list-style-type: none"> external / minimum 	19.2 V
<ul style="list-style-type: none"> external / maximum 	28.8 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.17 A

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation 	0 ... 60 °C
<ul style="list-style-type: none"> during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> during transport 	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP20

Design, dimensions and weight

Design	Box
Width	40 mm
Height	117 mm
Depth	109 mm
Net weight	0.25 kg
Material / of the enclosure	Plastic
Mounting type	
<ul style="list-style-type: none"> 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> wall mounting 	No
<ul style="list-style-type: none"> S7-300 rail mounting 	No
<ul style="list-style-type: none"> S7-1500 rail mounting 	No

Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of ≤ 0.3 s	50
Cascading in cases of star topology	any (depending only on signal propagation time)

Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> CLI 	Yes
<ul style="list-style-type: none"> web-based management 	Yes
<ul style="list-style-type: none"> MIB support 	Yes
<ul style="list-style-type: none"> TRAPs via email 	Yes
<ul style="list-style-type: none"> Configuration with STEP 7 	Yes
<ul style="list-style-type: none"> RMON 	Yes
<ul style="list-style-type: none"> Port mirroring 	Yes
<ul style="list-style-type: none"> multiport mirroring 	No

• CoS	Yes
• with IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
Telegram length / for Ethernet / maximum	1522 byte
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
• SysLog	Yes
• loopback diagnostics	Yes

Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	No

Product functions / DHCP

Product function	
• DHCP client	Yes

Product functions / Redundancy

Product function	
<ul style="list-style-type: none"> • Ring redundancy 	Yes
<ul style="list-style-type: none"> • High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	No
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • redundancy procedure STP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> • redundancy procedure MSTP 	No
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	No
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • Passive listening 	Yes

Product functions / Security

Product function	
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • Broadcast/Multicast/Unicast Limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes

Product functions / Time

Product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1

- for hazardous zone / from CSA and UL
- for emitted interference
- for interference immunity

ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
 EN 61000-6-4 (Class A)
 EN 61000-6-2

Standards, specifications, approvals / CE

Certificate of suitability / CE marking Yes

Standards, specifications, approvals / miscellaneous

Certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
• Railway application in accordance with EN 50155	No
• Railway application in accordance with EN 50124-1	No
• KC approval	Yes

Accessories

Further Information / Internet Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

Security information

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

01/16/2018