



## Part Electrical Specifications

Product	Compliance	Status	Channels	Gain (V/V)	Gain Error Max (%)	V <sub>s</sub> Min (V)	V <sub>s</sub> Max (V)	V <sub>CM</sub> (V)	I <sub>q</sub> Typ (mA)	Bandwidth Typ (-3dB)	V <sub>os</sub> Max (mV)	V <sub>os</sub> Drift Max (μV/°C)	Operating Temperature Range (°C)	CMRR Typ (dB)	Package Type
NCS213RMUTAG	Pb-free Halide free	NEW	1	50	±1	2.2	26	-0.3 to 26	0.04	0.09	±0.100	0.5	-40 to 125	120	UQFN-10
NCS213RSQT2G	Pb-free Halide free	Active	1	50	±1	2.2	26	-0.3 to 26	0.04	0.09	±0.100	0.5	-40 to 125	120	SC-88-6 / SC-70-6 / SOT-363-6
NCV213RSQT2G	AEC Qualified PPAP Capable Pb-free Halide free	NEW	1	50	±1.5	2.2	26	-0.3 to 26	0.04	0.09	±0.15	1.5	-40 to 125	115	SC-88-6 / SC-70-6 / SOT-363-6

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 9/19/2018