

Output coupler Relay coupler, 1 change-over contact 230 V AC/DC
 Overall width 6.2 mm Spring-type terminal (push-in) Thermal current 6A



Figure similar

Product brand name	SIRIUS
Product category	SIRIUS 3RQ3 coupling relays in slim design
Product designation	Coupling relays with relay output (not plug-in)
Design of the product	Output coupling link
Product type designation	3RQ3

General technical data	
Display version LED	Yes
Product component	
• Relay output	Yes
• semi-conductor output	No
Insulation voltage	
• for overvoltage category III according to IEC 60664	
— with degree of pollution 3 rated value	300 V
Surge voltage resistance rated value	4 kV
maximum permissible voltage for safe isolation	
• between control and auxiliary circuit	300 V

Percental drop-out voltage related to the input voltage	10 %
Protection class IP	IP20
Shock resistance • acc. to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
Vibration resistance • acc. to IEC 60068-2-6	6 ... 150 Hz: 2 g
Operating frequency maximum	72 000 1/h
Switching behavior	monostable
Mechanical service life (switching cycles) • typical	10 000 000
Electrical endurance (switching cycles) • at AC-15 at 230 V typical	100 000
Thermal current	6 A
Reference code • acc. to IEC 81346-2:2009 • acc. to DIN EN 61346-2	K K

Control circuit/ Control

Control supply voltage at AC • at 50 Hz rated value • at 60 Hz rated value	230 V 230 V
Control supply voltage frequency • 1 rated value • 2 rated value	50 Hz 60 Hz
Control supply voltage at DC • rated value	230 V
Operating range factor control supply voltage rated value at DC • initial value • Full-scale value	0.8 1.1
Operating range factor control supply voltage rated value at AC at 50 Hz • initial value • Full-scale value	0.8 1.1
Operating range factor control supply voltage rated value at AC at 60 Hz • initial value • Full-scale value	0.8 1.1
Switch-on delay time • at AC maximum • at DC maximum	9 ms 8 ms
Off-delay time	19 ms

Closing delay	
• at AC	12 ms
• at DC	8 ms
Opening delay	
• at AC	20 ms
• at DC	18 ms
Design of the relay operating mechanism	poled
Product component Plug-in socket	No

Short-circuit protection

Design of the fuse link	
• for short-circuit protection of the auxiliary switch required	fuse gG: 4 A

Auxiliary circuit

Type of switching contact	Changeover contact
Material of switching contacts	AgSnO ₂
Number of CO contacts	
• for auxiliary contacts	1
Operating current of auxiliary contacts at AC-15	
• at 24 V	3 A
• at 250 V	3 A
Operating current of auxiliary contacts at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
Contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)

Main circuit

Type of voltage	AC/DC
------------------------	-------

Inputs/ Outputs

Property of the output Short-circuit proof	No
---	----

Outputs

Ampacity of the output relay at AC-15	
• at 250 V at 50/60 Hz	3 A
Ampacity of the output relay at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A

Electromagnetic compatibility

EMC emitted interference	
• acc. to IEC 60947-1	ambience A (industrial sector)

EMI immunity	
<ul style="list-style-type: none"> • acc. to IEC 60947-1 	corresponds to degree of severity 3
Conducted interference	
<ul style="list-style-type: none"> • due to burst acc. to IEC 61000-4-4 	2 kV
<ul style="list-style-type: none"> • due to conductor-earth surge acc. to IEC 61000-4-5 	2 kV
<ul style="list-style-type: none"> • due to conductor-conductor surge acc. to IEC 61000-4-5 	1 kV
Field-bound parasitic coupling acc. to IEC 61000-4-3	10 V/m
Electrostatic discharge acc. to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge

Display

Display version	
<ul style="list-style-type: none"> • as status display by LED 	LED green

Connections/Terminals

Product function	
<ul style="list-style-type: none"> • removable terminal 	No
Type of electrical connection	
<ul style="list-style-type: none"> • for auxiliary and control current circuit 	PUSH-IN connection (spring-loaded connection)
Wire length	
<ul style="list-style-type: none"> • at AC maximum 	500 m
<ul style="list-style-type: none"> • at DC maximum 	1 000 m
Type of connectable conductor cross-sections	
<ul style="list-style-type: none"> • solid 	1x (0.25 ... 2.5 mm ²)
<ul style="list-style-type: none"> • finely stranded with core end processing 	1x (0.25 ... 1.5 mm ²)
<ul style="list-style-type: none"> • finely stranded without core end processing 	1x (0.25 ... 2.5 mm ²)
<ul style="list-style-type: none"> • at AWG conductors solid 	1 x (20 ... 14)
<ul style="list-style-type: none"> • at AWG conductors stranded 	1x (20 ... 14)
Connectable conductor cross-section	
<ul style="list-style-type: none"> • solid 	0.25 ... 2.5 mm ²
<ul style="list-style-type: none"> • finely stranded with core end processing 	0.25 ... 1.5 mm ²
<ul style="list-style-type: none"> • finely stranded without core end processing 	0.25 ... 2.5 mm ²
AWG number as coded connectable conductor cross section	
<ul style="list-style-type: none"> • solid 	20 ... 14
<ul style="list-style-type: none"> • stranded 	20 ... 14

Installation/ mounting/ dimensions

Mounting position	any
Mounting type	snap-on mounting
Height	93 mm
Width	6.2 mm
Depth	72.5 mm

Required spacing

- | | |
|------------------------------|------|
| • with side-by-side mounting | |
| — forwards | 0 mm |
| — Backwards | 0 mm |
| — upwards | 0 mm |
| — downwards | 0 mm |
| — at the side | 0 mm |
| • for grounded parts | |
| — forwards | 0 mm |
| — Backwards | 0 mm |
| — upwards | 0 mm |
| — at the side | 0 mm |
| — downwards | 0 mm |
| • for live parts | |
| — forwards | 0 mm |
| — Backwards | 0 mm |
| — upwards | 0 mm |
| — downwards | 0 mm |
| — at the side | 0 mm |

Ambient conditions**Installation altitude at height above sea level**

- | | |
|-----------|---------|
| • maximum | 2 000 m |
|-----------|---------|

Ambient temperature

- | | |
|--------------------|----------------|
| • during operation | -25 ... +60 °C |
| • during storage | -40 ... +85 °C |
| • during transport | -40 ... +85 °C |

Relative humidity

- | | |
|--------------------|-------------|
| • during operation | 10 ... 95 % |
|--------------------|-------------|

Certificates/approvals

General Product Approval	Declaration of Conformity	Marine / Shipping
--------------------------	---------------------------	-------------------



CCC



CSA



UL



EG-Konf.



DNVGL.COM/AF

other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ3018-2AF00>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ3018-2AF00>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RQ3018-2AF00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ3018-2AF00&lang=en





last modified:

05/17/2018