



Construction

Casing material:	Plastic
Overall dimensions mounted (WxDxH):	150 x 80 x 30 mm

Measuring system

Measuring range (Max):	960
Measuring range (Min):	170
Precision (of [Max]):	1 %
Readout:	1
Sensor:	D
Weighing units:	HB HL HRB HRC HV MPa

Functions

All measurement directions possible (360°):	yes
Automatic recognition of the impact sensor:	yes
Statistical function:	yes
Wireless printer connection:	yes

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Service

ISO calibration certificate:	961-131
------------------------------	---------

Category

Brand:	Sauter
Category:	Hardness testers
Product Group:	Electronic Leeb hardness tester

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	380 x 280 x 80 mm
Gross weight:	4,560 kg
Net weight:	340 g
Shipping method:	Parcel service