

# compact cylinder ADN-12-25-I-P-A

Part number: 536215

★ Core product range

FESTO



## Data sheet

| Feature                                    | Value  |
|--|--|
| Stroke                                     | 25 mm  |
| Piston diameter                            | 12 mm  |
| Piston rod thread                          | M3   |
| Cushioning                                 | P: Flexible cushioning rings/plates at both ends                                   |
| Assembly position                          | Any  |
| Conforms to standard                       | ISO 21287  |
| Piston-rod end                             | Female thread  |
| Position detection                         | For proximity sensor   |
| Variants                                   | Single-ended piston rod  |
| Operating pressure                         | 1 ... 10 bar   |
| Mode of operation                          | double-acting  |
| Operating medium                           | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                           |
| Note on operating and pilot medium         | Lubricated operation possible (subsequently required for further operation)        |
| Corrosion resistance classification CRC    | 2 - Moderate corrosion stress  |
| Ambient temperature                        | -20 ... 80 °C  |
| Impact energy in end positions             | 0.07 J   |
| Theoretical force at 6 bar, return stroke  | 51 N   |
| Theoretical force at 6 bar, advance stroke | 68 N   |
| Moving mass with 0 mm stroke               | 9 g  |
| Additional weight per 10 mm stroke         | 12 g   |
| Basic weight for 0 mm stroke               | 77 g   |
| Additional mass factor per 10 mm of stroke | 2 g  |
| Mounting type                              | Optional<br>with through hole<br>with internal (female) thread<br>with accessories |
| Pneumatic connection                       | M5   |
| Materials note                             | Conforms to RoHS   |
| Material cover                             | Aluminium<br>Anodised  |
| Material seals                             | TPE-U(PUR)   |
| Material piston rod                        | High alloy steel   |
| Material cylinder barrel                   | Wrought Aluminium alloy<br>Smooth anodised   |