

405-416-425-435- DIAGONAL CUTTERS




Standards :

NF ISO 9654, ISO 9654, DIN ISO 9654, ASME B107.500

Description :

- 405: Axial cut.
- 416 - 435: Semi-flush cut, slim nose.
- 425: Flush cut, nose extended 13 mm.
- Finish: Matt burnished finish, red grips - return spring.
- Copper only (for 405.10 and 405.12).



References :

	B [MM]	C [MM]	E [MM]	L [MM]	L1 [MM]	[G]
405.12	16,0	16,0	16,0	120	8	95
405.10	11,5	10,5	10,5	110	7	60
435	13,0	10,5	10,5	110	7	60
416	11,5	10,5	10,5	110	7	60
425	13,0	10,5	10,5	110	7	60